



- Designed for ISO : 7183-1986 (E)
- Dryer Quality Class ISO: 8573-1: 2010 (E) Class 2 (-40°C PDP)
- Pressure Drop <0.3 kg/cm<sup>2</sup> (g)
- Fabrication Code: IS 2825.
- LCD Display.
- Filter made of aluminium with differential pressure indicator.
- Inbuilt Sample gas chamber and electrical outlet for Miniature Dew point Transmitter.
- Operating Voltage:  $230 \pm 10 \% \text{ V AC } 50/60 \text{ Hz } 1 \text{ Ph.}$

Compressed Air Dryers (Heatless)

**DP V3 Series** 

# **Selection Example**

Requirement

Flow Volume : 480 cfm Working Pressure : 10 bar (g)

Inlet Air Temperature : 45°C

Referring the Graphs : Factor (P) = 1.4

Factor (T) = 0.67

Dryer capacity required:

Flow volume = 512 cfm Factor (T)  $\times$  Factor (P) 1.4  $\times$  0.67

Choose the nearest higher model i.e, Model DP 960 V3

Model	Item Code	Inlet Flow cfm	End Connection	Dimensions (mm)			Weight
				Height	Width	Depth	Kg
DP 768 V3	PD364	450	2" NB	1790	1120	870	520
DP 960 V3	PD365	565	2" NB	1760	1320	870	620
DP 1440 V3	PD366	850	3" NB	1910	1620	1020	940
DP 1920 V3	PD367	1130	3" NB	2010	1620	1020	1020

- For any other capacity contact factory.
- Specifications are subject to change without notification.

# **Specification**

Maximum Operating Pressure: 12.5 kg/cm<sup>2</sup> (g)

Rated Air Inlet Temperature: 38°C

Rated Operating Pressure : 7 kg/cm<sup>2</sup>

Pre - Filter Rating : 5 micron

After - Filter Rating : 1 micron

Cycle Time : 5 minutes


Purge Loss  $: 15 \pm 1\%$ 

Outlet Air Quality : -40°C PDP


### **Principle of Operation**

Drying Cycle: Moist air from the compressor is sent through the coalescing filter, there water & oil coalesces and purges through the auto drain valve. The relatively clean air with water vapor passes through the one of the towers filled with desiccant gets completely dried (upto -40°C PDP) and then passes through a built in After - filter (1 micron). The desiccant fines from the tower are completely removed and clean air is let out through the outlet port for use.


**Regeneration Cycle:** During the regeneration cycle, the sudden depressurisation brings out water molecule strapped in the Desiccant pores to the surface of the beads. A small portion of dry compressed air from the drying tower then passes over the desiccant through the regeneration orifice. This results in complete regeneration of the Desiccant.



#### **Inlet Pressure Correction Factor**



### **Inlet Temperature Correction Factor**





#### **Our Other Range of Products**

• Timer based Auto Drain Valve • Level Sensing Auto Drain Valve • Desiccant Dryer (Heated) • Refrigeration Dryers • Water Separator • Submicron Filter







#### **Trident Pneumatics Pvt Ltd**

5/232, K.N.G. Pudur Road, Coimbatore - 641 108, India. Ph : +91-422-2400492, 2401373 Fax : +91-422-2401376





Sales & Service Outlets